GC200S-T

High sensitivity Piezoelectric Accelerometer

- Shear design
- Piezoelectric ceramic PZT-5
- Sensitivity 200pC/g
- Mass 30grams
- 10-32UNF side entry connector
- Use with a Low noise cable

Specification	Metric	Imperial
Sensitivity	20.4pC/(m/s²)	200pC/g
Measurement Range (pk)	±4900m/s ²	±500g
Frequency Range ±10%	5000 Hz	
Resonant Frequency	≥20 kHz	
Non-Linearity	≤1 %	
Transverse Sensitivity	≤5 %	
Overload Limit (Shock)	±49033(m/s²)pk	±5000gpk
Operating Temp. Range	-54 to +150°C	-65 to +302°F
Polarity ↑	Positive	
Capacitance	700 pF	
Insulation Resistance	>1X10 ¹¹ Ω	
Size (excluding connector)	16(A/F)x23 mm	0.63"(A/F)x0.90"
Weight	30gm	1.06oz
Sensing Geometry	Shear	
Sensing Element Material	PZT-5	
Case Material	Titanium	
Connector Position	Side	
Case sealing	Welded	
Electrical Connection Type	10-32UNF Microdot	
Mounting Thread (tapped base)	10-32UNF	
Mounting Torque	3Nm	26in/lb

R


The GC200S-T is a high sensitivity monoaxial piezoelectric accelerometer with a side entry 10/32UNF microdot connector.


Piezoelectric Charge Output Accelerometer 200pC/g

The base of the accelerometer has a tapped hole with a 10/32UNF thread for compatibility with many industry applications.


Featuring a shear design PZT-5 sensing element the GC200S-T is supplied with a standard 10/32UNF mounting stud (other studs are available on request).

10-32UNF-2A









It is recommended that the GC200S-T is used with a low noise cable from Kemo's range to reduce triboelectric noise.

1A2-30 – 3m(10ft) 10/32UNF microdot to BNC plug 1A2-50 – 5m(15ft) 10/32/UNF microdot to BNC plug 1A1-30 – 3m(10ft) 10/32UNFmdot to 10/32UNFmdot 1A1-50 – 5m(15ft) 10/32UNFmdot to 10/32UNFmdot

Kemo Limited Unit 1, Dene Yard Green Street Green Road, Dartford, Kent. DA2 8DH www.kemo.com sales@Kemo.com

Iss.1 – February 2022